

FDA-160i

Advanced Distribution Amplifier



Features

- Network Enabled Analog
 Frequency Distribution Amplifier
- Dual Frequency Inputs with Auto Failover
- Any Frequency from 1-20MHz

The FDA-160i is a general-purpose frequency distribution amplifier designed for use with Brandywine high precision time and frequency sources.

The FDA-160i is contained in a compact IU rack-mount chassis. The FDA accepts two sets of inputs, comprising the reference frequency (typically 1-20MHz) and status from the source. The FDA provides automatic changeover should one of the online source inputs fail. Manual source select override is available on the front panel, or through the Ethernet interface.

A variety of status indicators are located on the front panel for instant visual feedback, together with manual controls for source selection.

- Programmable per channel amplitude
- 1U 19" rack mount
- Redundant Hot Swap Power Supplies

A 10/100 base T Ethernet interface provides full control over the functionality of the system, including reference selection and output amplitude (on a per channel basis).

User control of the unit is via a built-in Web Browser with user-friendly graphical interface, or via SNMP for system applications.

Applications for the FDA-160i include secure communications systems, manufacturing facilities, digital television broadcasting and any system requiring highly reliable frequency outputs.



FDA-160i Specifications

Frequency Inputs

Frequency 1-20~MHzAmplitude & Impedance $0.5\text{-}1\text{Vrms}, 50~\Omega$ Isolation Transformer coupled

Number of Inputs 2
Connector Type BNC
Input Selection Manual, Auto

Fault Inputs

Action

Number of Inputs 2 Signal Type TTL

Active Level Selectable for active

high or low Forces on-line changeover

Frequency Outputs

Number of Outputs 16

Frequency Same as Input 1-20 MHz

Output Level 5dBm to +13dBm, short-

circuit proof

Connector Type BNC
Harmonic Distortion -40 dBc
Cross Talk -80 dBc
Spurious -80 dBc

Additive Phase Noise@10MHz

TBD.

Network Interface

Interface Type 10/100 base T
Protocols HTTP, DHCP, IPV4
Connector RJ45

Connector
Console Port

Interface Type

Parameters 115200, N, 8, 1

Connector

Display

Display Type 16 bicolor LED

Functions Output status, Ethernet

settings

RS232

DB9

Status Output (Alarm)

Type Dry relay form C contacts

Ethernet SNMP trap

Alarm Function Summary of all input/output

alarms (relay)

Individual input, output, power

(Ethernet)

Power

Redundancy Dual redundant

Single supply maintains complete

ınit

Voltage 90-240 VAC 50/60Hz (std)

18-36V DC Optional 36-72VDC Optional

Power Consumption <15W

Environmental and Safety

Temperature

Operating -10 to +55°C non condensing

Storage -40 to +85°C

Product Safety EN60950-1: 2006 +

A11-2009 +A1:2010 A12:2011

EMC EN55022 Class A

EN50082-2

FCC Chapter 15 Class A

Ordering Information

Basic Unit Includes Dual AC Power Supplies 022050005 2 input, 16 output 1-20 MHz**

Power Options (order separately)

022060001 Substitute 18-36 DC power for AC 022060002 Substitute 36-72 DC power for AC

Related Product: FDU-160i:

022050001 2 i/p 10MHz, 16 output 10MHz 022050002 2 i/p 5MHz, 16 output 5MHz 022050003 2 i/p 1MHz, 16 output 1MHz

022050004 1ea i/p 5MHz,10MHz, 8 ea. o/p 5,10 MHz*

The FDA-160i may be used with many of Brandywine's precision frequency sources such as the RG 2111 for distribution of precision frequency outputs.

RG 2111 part number 001-0230

© Brandywine Communications 2014

^{*} No Auto-switch applicable to 022050004